

BRUNO

Offset Fold-Away™



Bruno R³™
Equipped

EXCLUSIVE R³ Lift Belt
is 50% Stronger –
an Industry First!

Bruno Model
ASL-450



Ideal for minivan and some SUV applications where space may be limited.



OPTIONAL BRUNO POW'RPAC



- ◆ Easy to use!
- ◆ Convenient!
- ◆ Works in most minivans, SUVs, station wagons & sedans!

The complete, independent power supply for your automotive lift!

Pow'rPac easily installs in your vehicle – just plug into the vehicle's power outlet!


- ◆ The Bruno Offset Fold-Away Vehicle Lift, Model ASL-450, eliminates the struggle of taking apart your trunk lift. This lift fits most sedans, hatchbacks and stationwagons and is ideal for smaller openings where space may be limited. It simply rotates and folds down into your trunk or hatch area.
- ◆ The Offset Fold-Away is designed to be installed on either the driver or passenger side, giving you the flexibility to load a partially-assembled scooter from the driver or passenger side as well as behind the vehicle bumper.
- ◆ Simply press a button on the pendant control and the Offset Fold-Away raises and lowers your mobility device.
- ◆ The effort needed to lift the Model ASL-450 mast is a mere 2-3 pounds and it features a dual-spring assist.
- ◆ It incorporates a low-resistance, pivot design making operation almost effortless.
- ◆ Color-keyed, hand grips make user operation simple and easy to follow.
- ◆ The Offset Fold-Away features Bruno's industry-leading, adjustable, low-profile outer arm and lifts up to 200 lbs./91 kg.
- ◆ **EXCLUSIVE!** Bruno's R³ Lift Belt is 50% stronger! Count on Bruno's R³ Lift Belt for ease of use, longer life and safer operation – *another Industry First!*
- ◆ Expert installation and complete, after-sale service is provided by Bruno's nationwide network of dealers.
- ◆ Only Bruno has over 25 different interior/exterior scooter, wheelchair and power chair lifts for nearly any sedan, hatchback, station wagon, convertible, minivan, sport utility vehicle (SUV), full-size van, pickup truck and the new cross-over vehicles.
- ◆ All Bruno Lifts are eligible for reimbursement under the terms of Mobility Programs offered by GM, Saturn, DaimlerChrysler/Dodge, Ford, Toyota, Lexus, Volvo and Volkswagen.

 **BRUNO**®
INDEPENDENT LIVING AIDS

Using the *Bruno Offset Fold-Away* is as easy as 1-2-3!



Just connect the exclusive Bruno docking device to the scooter and the OFFSET FOLD-AWAY can pick it up from the rear or at the side of the vehicle.



After raising the scooter using the pendant control, rotate the scooter over the trunk.




Guide the scooter into the trunk and put away the Lift. It's that easy!



Stored and ready to go! The Offset Fold-Away's compact design fits more vehicles.



Visual instruction guide mounted in the trunk makes operation a snap!



Color-keyed, outer-arm release assembly is easy to use.



Offset mast design requires only 2 lbs. of lifting effort! An industry first!



The Lift weight rating is the MAXIMUM load value. Factors inherent to specific applications including, but not limited to, vehicle structure and condition, operating environment, and customer ability may reduce the effective weight rating.

Represented By:



Bruno Independent Living Aids, Inc., 1780 Executive Drive,
P.O. Box 84, Oconomowoc, WI 53066

1-262-567-4990 ♦ FAX: 1-262-953-5501

www.bruno.com